









OFFICIAL DISTRIBUTOR MERCOFRAMES OPTICAL CORP

5555 NW 74 Ave. Miami, FL 33166. United States Phone: 305-882-0120 sales@mercoframes.net www.mercoframes.com HRM-001 operating microscope is our latest developed product for ophthalmic surgery. Equipped with advanced motorized continuous zoom, the instrument can meet the needs of ZOOM magnification during the operation.

The assistant scopes have tree ranges of magnification, and can be turned round the main scopes within 180° and be fixed at any angel. High resolution video camera mountable, and connect to monitor.



BIOM KIT mountable for HRM-001microscope, which can be used for retinal surgery.





BIOM Lens: 130°, 120°, 90° available BIOM size: 138*50*170mm Lens Position: Rotational assembly Mountable for Zeiss, Leica, Topcon, Takagi operating microscopes.

www.hansheiss.com

HRM001



TECHNICAL SPECIFICATIONS

MICROSCOPE	
Eyepiece	12.5X
Objective Lens	F=200mm (F175mm, F250mm, F300mm, F350mm, F400mm Optional)
Binocular Angle	30° to 90° adjustable
Working Distance	200mm
Main Scope Magnification	4.5X ~ 27X ZOOM
Assistant Scope Magnification	6.5X, 10.8X, 17.3X
Diameter of view-field for main scope	diameter 8mm ~ diameter 45mm
Diameter of view-field for assistant scope	diameter 12mm, diameter 19mm, diameter 31mm
Pupil Distance adjustable	55mm ~ 75mm (continuously adjustable)
Diopter Adjustable	± 6D
Fine-focus Speed & Range	≤ 2mm/s, ≥25mm
X/Y Moving Speed & Range	≤2mm/s, ≥30mm X 30mm
ILLUMINATION SYSTEM	
Illumination Type	6°+0°coaxial illumination of cold light source
Illumination Source	15V/150W, cold reflection halogen lamp
Illumination Adjustment	Digital controllable continuously
Coaxial Illumination	≥ 800000 LX
STANDING FRAME	
Extension Range of ARM	1200mm
Vertical Adjusting Range	450mm