




Types of Chart



Free voltage & Free frequency

By applying SMPS, it can show a steady chart brightness that is not almost affected by the changes of AC voltage input.

Body channel is operated by remote control

Body channel was operated on the previous product through the switch of the body. But body channel can be easily operated on the new product only by the remote control.

Clear & various charts.

It shows clear 42 charts, including eyesight, astigmatic angle, binocular vision, heterophoria, stereopsis and so on, and the mask (vertical, horizontal, single).

Rapid chart change speed

We can provide rapid and comfortable optometry service to the customers with the chart change speed of the industry top level.

Refined & outstanding design

The refined appearance, which shows LED lighting at the side of the product, will upgrade the optometry room.

HHCP-8000L

High luminance LED can provide a clearer chart than halogen lamp and reduces the maintenance effort.

SPECIFICATIONS

Charts	
Charts	42 EA
Distance of Projector	2.5~8m
Chart magnification	30× (when projected at 5m distance)
Lamp	LED lamp
Masks	35EA (1 open mask, 5 horizontal line maksks, 8 vertical line masks, 21 single letter masks)
Filter	1 Red/Green Filter
Chart rotation speed	average 0.2 sec (min. 0.092sec, max.0.324sec)
Power supply	AC100-240V, 50/60Hz
Power consumption	60VA
Dimensions	Main Body (Stand Excluded) : 202(W)×364(D)×240(H) mm Remote Controller : 64(W)×196(D)×20(H) mm
Weights	Main Body (Stand Excluded) : 4.7 kg Remote Controller : 160 g (Battery included)
Basic accessories	Product Body, Screen, Remoto Controller, Table Stand, Dust Cover, Power Cable T wrench, Fuse, Battery
Optional accessories	Red/Green glasses, Polarization glassesy

